




MA-MH-ML 630/1250 MA-MH 630/1600ES MS 630/1600



- 1) Leva di comando
 - 2) Tasto di prova meccanica
 - 3) Regolazione termica e magnetica
-
- 1) Betätigungshebel
 - 2) Prüftaste für mechanische Kontrolle
 - 3) Einstellung der thermomagnetischen Auslösern
-
- 1) Manette de commande
 - 2) Bouton de test mécanique
 - 3) Réglage des déclencheurs magnéto-thermiques
-
- 1) Operating handle
 - 2) Push-to-trip button for mechanical checking
 - 3) Setting of thermal-magnetic releases
-
- 1) Planca de accionamiento
 - 2) Pulsador de prueba para la verificación mecánica
 - 3) Regulación térmica y magnética



	S
MA-MH-ML 1250	≥ 1000 A
MA-MH-ML 1250/1600ES	≥ 1000 A
MS 1250/1600	≥ 1000 A
MA-MH-ML 630/800	< 1000 A
MA-MH-ML 630/800ES	< 1000 A
MS 630/800	< 1000 A

	3P	4P
A	210	280
B	70	-
C	-	140

